

M-10iD/8L



Max. load capacity at wrist: 8 kg



Max. reach: 2032 mm

FANUC

| Robot | | | Max. load capacity at wrist (kg) | Reach (mm) | Controlled axes | Repeatability (mm) | Mechanical weight (kg) | Motion range (°) | | | | | | Maximum speed (°/s) | | | | | | Moments (N-m)/Inertia (kg-m ²) | | | Protection | | |
|--------|---------|------|----------------------------------|------------|-----------------|--------------------|------------------------|------------------|-----|-----|-----|-----|-----|---------------------|-----|-----|-----|-----|-----|--|-------------------|-------------------|--------------------------------|------------------------|----------------------------------|
| Series | Version | Type | | | | | | J1 | J2 | J3 | J4 | J5 | J6 | J1 | J2 | J3 | J4 | J5 | J6 | J4 Moment/Inertia | J5 Moment/Inertia | J6 Moment/Inertia | Average Power consumption (kW) | Body standard/optional | Wrist & J3 arm standard/optional |
| M-10 | iD | 8L | 8 | 2032 | 6 | ±0.03** | 180 | 340 (370) | 235 | 455 | 380 | 360 | 900 | 210 | 210 | 220 | 430 | 450 | 720 | 16.1/.63 | 16.1/.63 | 5.9/.061 | 1 | IP54 | IP67 |

● standard ○ on request - not available ** Based on ISO9283

M-10iD/8L Extra Long Arm, Hollow Wrist



M-10iD/8L

