

# M-710iC/50T



Max. load capacity at wrist: 50 kg




Max. reach: 1900 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
M-710	iC	50T	50	1900 <sup>*1</sup>	6	± 0.07	410	*1	261	491	720	250	720	*1	175	175	250	250	355	206/28	206/28	127/11	2.5	IP54/ IP67	IP67

● standard ○ on request - not available \*1 depending on rail specification

M-710iC/50T Top mount



M-710iC/50T

