

M-900iB/700E



Max. load capacity at wrist: 700 kg



Max. reach: 2832 mm

FANUC

| Robot | | | Max. load capacity at wrist (kg) | Reach (mm) | Controlled axes | Repeatability (mm) | Mechanical weight (kg) | Motion range (°) | | | | | | Maximum speed (°/s) | | | | | | Moments (N-m)/Inertia (kg-m ²) | | | | Protection | |
|--------|---------|------|----------------------------------|------------|-----------------|--------------------|------------------------|------------------|-----|-----|-----|-----|-----|---------------------|----|----|-----|-----|-----|--|-------------------|-------------------|--------------------------------|------------------------|----------------------------------|
| Series | Version | Type | | | | | | J1 | J2 | J3 | J4 | J5 | J6 | J1 | J2 | J3 | J4 | J5 | J6 | J4 Moment/Inertia | J5 Moment/Inertia | J6 Moment/Inertia | Average Power consumption (kW) | Body standard/optional | Wrist & J3 arm standard/optional |
| M-900 | iB | 700E | 700 | 2832 | 6 | ± 0.1** | 3030 | 360 | 154 | 160 | 720 | 244 | 720 | 80 | 80 | 80 | 100 | 100 | 160 | 5000/1098 | 5000/1098 | 2800/444 | 5 | IP54/ IP56 | IP67 |

● standard ○ on request - not available | with hardware and/or software option ** Based on ISO9283

M-900iB/700E Standard model



M-900iB/700E

