

M-20iD/25

FANUC



Max. load capacity
at wrist: 25 kg



Max. reach:
1831 mm

Series	Robot	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						Protection					
									J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6						
M-20	iD	25	25	25	1831	6	±0.02**	250	340 (370)	260	458	400	360	900	210	210	265	420	420	720	52/2.4	52/2.4	32/1.2	1	IP54/ IP65	Wrist & J3 arm standard/optional

● standard

○ on request

- not available

** Based on ISO9283

M-20iD/25

Hollow Wrist



M-20iD/25

