

# M-10iD/12



Max. load capacity at wrist: 12 kg



Max. reach: 1441 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m <sup>2</sup> )			Protection		
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption (kW)	Body standard/optional	Wrist & J3 arm standard/optional
M-10	iD	12	12	1441	6	±0.02**	145	340 (370)	235	455	380	360	900	260	240	260	430	450	720	26/9	26/9	11/3	1	IP54/ IP65	IP67

● standard ○ on request - not available \*\* Based on ISO9283

M-10iD/12

Hollow Wrist



M-10iD/12

