

LR Mate 200iD/14L



Max. load capacity
at wrist: 14kg



Max. reach:
911 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						Maximum speed [°/s]						J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
LR Mate 200	iD	14L	14	911 820*	6	± 0.01**	27	340 (360)	245	430	380	250	720	120	61	58	400	240	400	31/.66	31/.66	13.4/.30	0.5	IP67/ IP69K	IP67/ IP69K

[option] ● standard ○ on request - not available [] with hardware and/or software option ** Based on ISO9283 *load capacity 12KG or less

LR Mate 200iD/14L Long arm, heavier payload



LR Mate 200iD

