

# LR Mate 200iD/4SC

**FANUC**

Max. load capacity  
at wrist: 4 kg

Max. reach:  
550 mm

Series	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption [kW]	Protection
								J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					
LR Mate 200	iD	4SC	4	550	6	± 0.01**	20	340 (360)	230	402	380	240	720	460	460	520	560	560	900	8.86/ 0.2	8.86/ 0.2	4.9/ 0.067	0.5	IP67

(option)

● standard

○ on request

- not available

{ } with hardware and/or software option

\*\* Based on ISO9283

LR Mate 200iD/4SC Short arm, clean room, food grade grease  
(2 integrated solenoid valves)



LR Mate 200iD

