

## LR Mate 200iD/4SH



Max. load capacity  
at wrist: 4 kg



Max. reach:  
550 mm

Series	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption [kW]	Protection
								J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					
LR Mate 200	iD	4SH	4	550	5	± 0.01**	19	340 (360)	230	402	240	720	-	460	460	520	560	1500	-	8.86/ 4/.046	4/.046	-	0.5	IP67

(option)

● standard

○ on request

- not available

{ } with hardware and/or software option

\*\* Based on ISO9283

LR Mate 200iD/4SH      Short arm, 5-axis  
(2 integrated solenoid valves)



LR Mate 200iD

