

M-900/330F-32B



Max. load capacity at wrist: 330 kg



Max. reach: 3203 mm

FANUC

Robot		Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-900	B	330	3203	6	± 0.1**	1780	370	151	164	720	250	720	100	85	85	90	85	165	2205/340	2205/340	1200/220	3	IP54/ IP56	IP67

● standard ○ on request - not available () with hardware and/or software option ** Based on ISO9283

M-900/330F-32B Long arm



M-900/330F-32B

