

CR-35iA



Max. load capacity at wrist: 35 kg



Max. reach: 1813 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Average Power consumption (kW)	Protection				
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6		J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Body standard	Wrist & J3 arm
CR	iA	35	35	1813	6	±0.03**	990	340/370***	165	258	400	220	900	250*	250*	250*	250*	250*	250*	110/4	110/4	60/1.5	0.5	IP54	IP67

● standard ○ on request - not available * max. cartesian speed 750mm/sec ** Based on ISO9283 ***Option

CR-35iA Standard Model



CR-35iA

