

# M-410iB/700



Max. load capacity at wrist: 700 kg



Max. reach: 3143 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
M-410	iB	700	700	3143	4	±0.05**	2700	360	144	136	540	-	-	60	60	60	120	-	-	490	-	-	3	IP54	IP54

● standard ○ on request - not available \*\* Based on ISO9283

M-410iB/700

Hollow wrist



M-410iB/700

