

M-710iC/20L

FANUC



Max. load capacity
at wrist: 20 kg




Max. reach:
3110 mm

Series	Robot		Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption [kW]	Protection
	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					
M-710	iC	20L	20	3110	6	± 0.06**	540	360	225	432	400	280	900	175	175	180	350	360	600	39.2/.88	39.2/.88	19.6/.25	2.5	IP54/IP67

● standard ○ on request - not available ** Based on ISO9283

M-710iC/20L

Long arm



M-710iC/20L

