

M-900iB/700



Max. load capacity at wrist: 700 kg



Max. reach: 2800 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
M-900	iB	700	700	2832	6	± 0.1**	2800	360	154	160	720	244	720	80	80	80	100	100	160	3400/1098	3400/1098	1725/444	5	IP54/ IP56	IP67

● standard ○ on request - not available () with hardware and/or software option ** Based on ISO9283

M-900iB/700

Standard model



M-900iB/700

