

R-2000iC/220U



Max. load capacity
at wrist: 210 kg



Max. reach:
2518 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
R-2000	iC	220U	220	2518	6	±0.05**	1020	370	136	312	720	250	720	120	85	110	140	140	220	1360/147	1360/147	735/82	3	IP54	IP67

● standard ○ on request - not available () with hardware and/or software option *1) depending on rail specification ** Based on ISO9283

R-2000iC/220U

Upside down mount



R-2000iC/220U

