

## SR-12iA Environmental Option



Max. load capacity  
at wrist: 12 kg



Max. reach:  
900 mm


Series	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						Moments [N·m]/Inertia [kg·m <sup>2</sup> ]		Protection	
								J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	Push Force [N]	Body standard/optional	Wrist & J3 arm standard/optional
SR	iA	12	12	900	4	± 0.01 [J1, 2] ± 0.01 [J3] ± 0.005° [J4]	53	±145	±145	300 mm* (450 option)	±720	-	-	440	510	2800 mm/s	2500	-	-	-/0.3	250	IP65	IP65

- not available

\* z axis

SR-12iA

4-axis Environmental Option



SR-12iA