

SR-3iA/H

FANUC

Max. load capacity
at wrist: 3 kg


Max. reach:
400 mm

Series	Version	Type	Robot		Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						Moments [N·m]/Inertia [kg·m ²]		Protection		
			Max.load capacity at wrist [kg]	Reach [mm]				J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J4 Moment/Inertia			
SR	iA/H	3	3	400	3	$\pm 0.01 [J1, J2]$ $\pm 0.01 [J3]$	17	± 142	± 145	200 mm*	-	-	-	720	780	1800 mm/s*	-	-	-	-0.06	-	150	IP20	IP20

- not available

* z axis

SR-3iA/H 3-axis



SR-3iA/H