

# CR-35iB

**FANUC**



Max. load capacity  
at wrist: 35/50\* kg



Max. reach:  
1831 mm

Robot			Series	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	****Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						***Maximum speed [°/s]		J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption [kW]	Protection
J1	J2	J3	J4	J5	J6	Collaborative Mode [mm/sec]	High Speed Mode [mm/sec]																
CR	iB	35	35 50*	1831 1643**	6	± 0.03	375	370	215	338	400	280	900	750	750	110/ 4	110/ 4	60/ 1.5	1	IP54	IP67	Body standard	Wrist & J3 arm

● standard    ○ on request    - not available    \*Option required    \*\*Operating space is restricted when 50kg payload mode is selected    \*\*\*Please set motion speed according to risk assessment of system.    \*\*\*\*Based on ISO9283

CR-35iB

Standard Model



CR-35iB

