

# SR-3iA/C



Max. load capacity at wrist: 3 kg



Max. reach: 400 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m <sup>2</sup> )			Push Force (N)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia				Body standard/optional	Wrist & J3 arm standard/optional
SR	iA/C	3	3	400	4	±0.01 (J1, J2) ±0.01 (J3) ±0.004° (J4)	21	±142	±145	200 mm*	±720	-	-	720	780	1800 mm/s	3000	-	-	-/0.06	,	,	150	IP54	IP54

- not available \* z axis

SR-3iA/C

4-axis, food grade grease, ISO Class 2 - ISO Class 5



SR-3iA/C

