

SR-3iA/U



Max. load capacity
at wrist: 3 kg





Max. reach:
350 mm

FANUC

Series	Robot		Max.load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m²)			Push Force (N)	Protection	
	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia				Body standard/optional	Wrist & J3 arm standard/optional
SR	iA/U	3	3	350	4	± 0.01(J1, J2) ± 0.01 (J3) ± 0.004° (J4)	27	±225	±225	140 mm	±720	-	-	610	840	1500 mm/s*	3000°/s	-	-	-/0.06	,	,	150	IP20	IP20

- not available * z axis

SR-3iA/U 4-axis



SR-3iA/U