

LR Mate/10-11A Food/Clean



Max. load capacity
at wrist: up to 13kg



Max. reach:
1101 mm

FANUC

Robot		Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard/optional	Wrist & J3 arm standard/optional
LR Mate	A	10 13*	1101	6	±0.01**	46	370	235	421	380	250	720	300	230	340	500	400	800	21/ 0.77	21/ 0.77	10/ 0.28	0.5	IP67	IP67

- not available

* Payload can be up to 13kg with restricted envelope

** Based on ISO9283

LR Mate/10-11A Food/Clean

Clean room, food grade grease
(2 integrated solenoid valves)



LR Mate/10-11A Food/Clean

