

M-810/270-27B



Max. load capacity
at wrist: 270 kg



Max. reach:
2687 mm

FANUC

Robot		Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)***						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-810	B	270	2687	6	±0.03*	1430**	330	171	312	306	240	720	100	80	80	120	115	200	1730/320	1730/320	900/230	3	IP54/ IP56	IP67

● standard ○ on request - not available * Meets ISO 9283 standards ** Without Controller *** During short distance motions, the axis speed may not reach the maximum value stated

M-810/270-27B

High accuracy model



M-810/270-27B

