

# M-900iB/360E



Max. load capacity at wrist: 360 kg



Max. reach: 2655 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m <sup>2</sup> )			Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-900	iB	360E	360	2655	6	±0.1**	1540	370	151	224	720	250	720	110	105	100	110	110	180	2330/500	2330/500	1280/360	3	IP54/ IP56	IP67

● standard ○ on request - not available ( ) with hardware and/or software option \*\* Based on ISO9283

M-900iB/360E

Standard model



M-900iB/360E

Rear side Interference area

