

R-2000iC/220U



Max. load capacity at wrist: 210 kg



Max. reach: 2518 mm


FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s) ***						Moments (N-m)/Inertia (kg-m ²)			Protection		
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption (kW)	Body standard/optional	Wrist & J3 arm standard/optional
R-2000	iC	220U	220	2518	6	± 0.05*	1020**	370	136	312	720	250	720	120	85	110	140	140	220	1360/147	1360/147	735/82	3	IP54	IP67

● standard ○ on request - not available * Based on IS09283 ** Without controller *** During short distance motions, the axis speed may not reach the maximum value stated.

R-2000iC/220U

Upside down mount



R-2000iC/220U

