

CR-35iB



Max. load capacity
at wrist: 35/50* kg



Max. reach:
1831 mm

FANUC

Robot			Max load capacity at wrist (kg)	Reach (mm)	Controlled axes	****Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						***Maximum speed [°/s]		J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	Collaborative Mode (mm/sec)	High Speed Mode (mm/sec)					Body standard	Wrist & J3 arm
CR	iB	35	35 50*	1831 1643**	6	± 0.03	375	370	215	338	400	280	900	750	750	110/ 4	110/ 4	60/ 1.5	1	IP54	IP67

● standard

○ on request

- not available

*Option required

**Operating space is restricted when 50kg payload mode is selected

***Please set motion speed according to risk assessment of system.

****Based on ISO9283

CR-35iB

Standard Model



CR-35iB

