

# SR-9iA/R



Max. load capacity at wrist: 9 kg





Max. reach: 620 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m <sup>2</sup> )	Push Force (N)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6			J4 Moment/Inertia	Body standard/optional
SR	iA/R	9	9	620	4	±0.01 (J1, J2) ±0.01 (J3) ±0.004° (J4)	76	±180	±150	200 mm (400mm option)	±720	-	-	560	480	2800 mm/s*	2500°/s	-	-	--/0.12	-	IP20	IP20

- not available \* z axis

SR-9iA/R 4-axis



SR-9iA/R