1-Axis Positioner for 1500 kg Payload (Hollow Type)

Max. payload capacity: 1500 kg

FANUC

Installation	Payload capacity (kg)	Controlled axes	Motion range (°)*	Repeatability (mm)**	Mass (kg)	Maximum speed (°/s)***	Flange hollow diameter (mm)	Allowable Load Moment (N·m)	Allowable Bending Moment (N·m)	Allowable Load Inertia (kg·m2)	Unit IP rating
Floor, Wall mount, Upside-down	1500	1	740 (±370)	± 0.02	280	150	120	2254	20580	1000	IP54

* Continuous turn option is available ** Compliant with ISO 9283 (R=500mm) *** During short distance motions, the axis speed may not reach the a maximum value stated

1-Axis Positioner	1500 kg Payload; Hollow Type







* w/Motor cover and HARTING connector option

OPTIONS:	Motor cover w/HARTING connector option	Continuous turn signal/earth cable option	Follower unit option