1-Axis Positioner for 300 kg Payload (Hollow Type)

Max. payload capacity: 300 kg

FANUC

Installation	Payload capacity (kg)	Controlled axes	Motion range (°)*	Repeatability (mm)**	Mass (kg)	Maximum speed (°/s)***	Flange hollow diameter (mm)	Allowable Load Moment (N·m)	Allowable Bending Moment (N·m)	Allowable Load Inertia (kg·m2)	Unit IP rating
Floor, Wall mount, Upside-down	300	1	740 (±370)	± 0.02	82	100V Input: 80 200V Input: 115	108	353	4000	230	-

* Continuous turn option is available ** Compliant with ISO 9283 (R=500mm) *** During short distance motions, the axis speed may not reach the a maximum value stated

1-Axis Positioner 300 kg Payload; Hollow Type







OPTIONS: Follower unit option

Compatible with CRX on R-30*i*B Mini Plus Controller