

CR-35iA



Max. load capacity
at wrist: 35 kg



Max. reach:
1813 mm

FANUC

Robot			Max.load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						Maximum speed [°/s]						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard	Wrist & J3 arm
CR	iA	35	35	1813	6	± 0.03**	990	340/ 370***	165	258	400	220	900	250*	250*	250*	250*	250*	250*	110/ 4	110/ 4	60/ 1.5	1	IP54	IP67

● standard ○ on request - not available * max. cartesian speed 750mm/sec ** Based on ISO9283 ***Option

CR-35iA

Standard Model



CR-35iA

