M-800*i*B/60

Max. load capacity at wrist: 60 kg

Max. reach: 2040 mm

FANUC

Robot								Motion range (°)						Maximum speed (°/s)									Protection	
Series	Version	Type	Max.load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Body	Wrist & J3 arm
M-800	*i*B	60	60	2040	6	±0.015*	820	370	225	340	720	250	720	150	150	150	260	260	400	210/ 30	210/ 30	130/ 20	-	IP54	IP54

● standard ○ on request - not available ( ) with hardware and/or software option * Meets ISO9283 standards

M-800*i*B/60 High accuracy model



M-800*i*B/60

