

M-20iA/12L



Max. load capacity at wrist: 12 kg



Max. reach: 2009 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
M-20	iA	12L	12	2009	6	±0.03**	250	(340) 370	260	460	400	360	900	200	175	190	430	430	630	22/1.65	22/1.65	9.8/1.17	1	IP54/ IP55	IP67

● standard ○ on request - not available ** Based on ISO9283

M-20iA/12L Long arm, hollow wrist



M-20iA/12L

