

M-430iA/2P



Max. load capacity at wrist: 2 kg



Max. reach: 700 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/Inertia (Nm/kgm ²)	J5 Moment/Inertia (Nm/kgm ²)	J6 Moment/Inertia (Nm/kgm ²)	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard optional	Wrist & J3 arm standard/optional
M-430	iA	2P	2	700	6	± 0.5	45	360	230	400	380	300	540	300	320	340	300	300	720	3.5/0.032	3.5/0.032	1.5/0.0065	1	IP67	IP67

● standard ○ on request - not available [] with hardware and/or software option

M-430iA/2P

6-axis



M-430iA/2P

