

# M-430iA/2PH



Max. load capacity at wrist: 2 kg



Max. reach: 900 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/Inertia (Nm/kgm <sup>2</sup> )	J5 Moment/Inertia (Nm/kgm <sup>2</sup> )	J6 Moment/Inertia (Nm/kgm <sup>2</sup> )	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard optional	Wrist & J3 arm standard/optional
M-430	iA	2PH	2	900	6	± 0.5	57	360	230	383	380	300	540	300	320	320	500	500	1700	3.5/0.032	3.5/0.032	1.5/0.0065	1	IP67	IP67

● standard ○ on request - not available [ ] with hardware and/or software option

M-430iA/2PH 6-axis



M-430iA/2PH

