

M-430iA/4FH



Max. load capacity at wrist: 4 kg



Max. reach: 900 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/Inertia (Nm/kgm ²)	J5 Moment/Inertia (Nm/kgm ²)	J6 Moment/Inertia (Nm/kgm ²)	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard optional	Wrist & J3 arm standard/optional
M-430	iA	4FH	4	900	5	± 0.5	55	360	230	383	300	540	-	300	320	320	360	2000	-	3.5/0.064	0/0.01	-	1	IP67	IP67

● standard ○ on request - not available () with hardware and/or software option

M-430iA/4FH 6-axis



M-430iA/4FH

