

M-710iC/50H



Max. load capacity
at wrist: 50 kg



Max. reach:
2003 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard optional	Wrist & J3 arm standard/optional
M-710	iC	50H	50	2003	5	±0.03**	540	360	225	440	234	720	-	175	175	175	175	720	-	150/6.3	68/2.5	-	2.5	IP54/ IP67	IP67

● standard ○ on request - not available v ** Based on ISO9283

M-710iC/50H 5-axis



M-710iC/50H

