

R-2000iC/210L



Max. load capacity
at wrist: 210 kg



Max. reach:
3100 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
R-2000	iC	210L	210	3100	6	±0.05**	1350	370	136	301	720	250	720	105	90	85	120	120	200	1700/320	1700/320	900/230	2.5	IP54 / IP56	IP67

● standard ○ on request - not available () with hardware and/or software option *1) depending on rail specification ** Based on ISO9283

R-2000iC/210L Long arm



R-2000iC/210L

