

M-800iA/60



Max. load capacity at wrist: 60 kg



Max. reach: 2040 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body	Wrist & J3 arm
M-800	iA	60	60	2040	6	±0.015*	820	370	225	340	720	250	720	150	150	150	260	260	400	210/30	210/30	130/20	-	IP54	IP54

● standard ○ on request - not available [] with hardware and/or software option * Meets ISO9283 standards

M-800iA/60

High accuracy model



M-800iA/60

