

1-Axis Positioner for 2000 kg Payload (Compact Type)



Max. payload
capacity: 2000 kg

FANUC

Installation	Payload capacity (kg)	Controlled axes	Motion range [°]*	Repeatability (mm)**	Mass (kg)	Maximum speed [°/s]***	Flange hollow diameter (mm)	Allowable Load Moment (N·m)	Allowable Bending Moment (N·m)	Allowable Load Inertia (kg·m ²)	Unit IP rating
Floor, Wall mount, Upside-down	2000	1	740 (±370)	± 0.02	120	120	N/A	2740	7056	1500	IP54





* Continuous turn option is available

** Compliant with ISO 9283 (R=500mm)

*** During short distance motions, the axis speed may not reach the a maximum value stated

1-Axis Positioner

2000 kg Payload; Compact Type



* w/Motor cover and HARTING connector option

OPTIONS:

Motor cover w/HARTING connector option

Follower unit option