

1-Axis Positioner for 5000 kg Payload



Max. payload
capacity: 5000 kg

FANUC

Installation	Payload capacity (kg)		Controlled axes	Motion range (°)*	Repeatability (mm)**	Mass (kg)	Maximum speed (°/s)***	Flange hollow diameter (mm)	Allowable Load Moment (N·m)		Allowable Bending Moment (N·m)	Allowable Load Inertia (kg·m ²)		Unit IP rating
	Floor	Wall Mount							Floor	Wall Mount		Floor	Wall Mount	
Floor, Wall mount	5000	1000	1	370(±185)	± 0.02	354	110	120	N/A	2100	34300	2500	1000	IP54





* Continuous turn option is available

** Compliant with ISO 9283 (R=500mm)

*** During short distance motions, the axis speed may not reach the a maximum value stated

1-Axis Positioner

5000 kg Payload



* Max. width with options
** Max. height with options

OPTIONS:

Clamp option

Motor cover option

HARTING connector option

Continuous turn signal cable option