

1-Axis Positioner for 500 kg Payload (Hollow Type)



Max. payload
capacity: 500 kg

FANUC

Installation	Payload capacity (kg)	Controlled axes	Motion range (°)*	Repeatability (mm)**	Mass (kg)	Maximum speed (°/s)***	Flange hollow diameter (mm)	Allowable Load Moment (N·m)	Allowable Bending Moment (N·m)	Allowable Load Inertia (kg·m ²)	Unit IP rating
Floor, Wall mount, Upside-down	500	1	740 (±370)	± 0.02	85	160	108	735	4000	360	IP54




* Continuous turn option is available

** Compliant with ISO 9283 (R=500mm)

*** During short distance motions, the axis speed may not reach the a maximum value stated

1-Axis Positioner

500 kg Payload; Hollow Type



* w/Motor cover and HARTING connector option

** w/Continuous turn cable option

OPTIONS:

Motor cover w/HARTING connector option

Continuous turn signal/earth cable option

Follower unit option