

2-Axes Positioner for 500 kg Payload



Max. payload
capacity: 500 kg



FANUC

Installation	Payload capacity (kg)	Controlled axes	Motion range (°)		Repeatability (mm)**	Mass (kg)	Maximum speed (°/s)***		Allowable Load Moment (N·m)		Allowable Load Inertia (kg·m2)		Unit IP rating
			J1	J2			J1	J2	J1	J2	J1	J2	
Floor, Wall mount, Upside-down	500	2	270 (±135)	480 (±240)*	± 0.05	295	120	190	1764	686	300	100	IP54


* Continuous turn option is available (J2 only) ** Compliant with ISO 9283 (R=500mm) *** During short distance motions, the axis speed may not reach the a maximum value stated

2-Axes Positioner

500 kg Payload



J1-axis rotation



(NOTE) The J2-axis has no mechanical stopper.

J2-axis rotation

