

Small Payload Handling Intelligent Robot

FANUC Robot M-10iD

FANUC Robot M-20iD



Features

FANUC Robot M-10iD / M-20iD is a cable integrated small payload handling robot.


The unique gear drive mechanism delivers high inertia with cable integration into the slim arm of the robot.

- The cables and tubes backside the tool control box can be integrated in the enlarged J1 hollow tube.
- Various cables and tubes used for gripper control can be integrated in the J3 arm due to the enlarged J4 and J6 hollow tubes. The tool control box can be compactly mounted on the backside of the J3 arm.
- Higher rigidity of the arm provides high speed and high accuracy of the robot motion, and can enhance the productivity of the system.
- Off-line teaching by ROBOGUIDE (Option) reduces touch-up cost.
- Various intelligent functions such as *iR*Vision (integrated vision) and force sensor are available.






Operating space

M-10iD/12, /10L, /8L



M-20iD/25



Specifications

Model		M-10iD/12	M-10iD/10L	M-10iD/8L	M-20iD/25
Control axes		6 axes (J1, J2, J3, J4, J5, J6)			
Reach		1441 mm	1636 mm	2032 mm	1831 mm
Installation		Floor, Upside-down, Angle mount *Floor, Upside-down for 4 brake type	Floor, Upside-down, Angle mount		
Motion range (Maximum speed) Note 1, 2)	J1 axis rotation	340° / 370°(Option)(260°/s) 5.93 rad / 6.46 rad(Option)(4.54 rad/s)		340° / 370°(Option)(210°/s) 5.93 rad / 6.46 rad(Option)(3.67 rad/s)	
	J2 axis rotation	235° (240°/s) 4.10 rad (4.19 rad/s)		235° (210°/s) 4.10 rad (3.67 rad/s)	260° (210°/s) 4.54 rad (3.67 rad/s)
	J3 axis rotation	455° (260°/s) 7.94 rad (4.54 rad/s)		455° (220°/s) 7.94 rad (3.84 rad/s)	
	J4 axis wrist rotation	380° (430°/s) 6.63 rad (7.50 rad/s)		400° (420°/s) 6.98 rad (7.33 rad/s)	
	J5 axis wrist swing	360° (450°/s) 6.28 rad (7.85 rad/s)		360° (420°/s) 6.28 rad (7.33 rad/s)	
	J6 axis wrist rotation	900° (720°/s) 15.71 rad (12.57 rad/s)			
Max load capacity at wrist		12 kg	10 kg	8 kg	25 kg
Allowable load moment at wrist	J4 axis	26.0 N·m	22.0 N·m	16.1 N·m	52.0 N·m
	J5 axis	26.0 N·m	22.0 N·m	16.1 N·m	52.0 N·m
	J6 axis	11.0 N·m	9.8 N·m	5.9 N·m	32.0 N·m
Allowable load inertia at wrist	J4 axis	0.90 kg·m ²	0.65 kg·m ²	0.63 kg·m ²	2.40 kg·m ²
	J5 axis	0.90 kg·m ²	0.65 kg·m ²	0.63 kg·m ²	2.40 kg·m ²
	J6 axis	0.30 kg·m ²	0.17 kg·m ²	0.061 kg·m ²	1.20 kg·m ²
Repeatability Note 3)		± 0.02 mm	± 0.03 mm		± 0.02 mm
Mass Note 4)		145 kg	150 kg	180 kg	250 kg
Installation environment		Ambient temperature : 0 to 45°C Ambient humidity : Normally 75%RH or less (No dew nor frost allowed), Short term 95%RH or less (within one month) Vibration acceleration : 4.9m/s ² (0.5G) or less			

Note 1) In case of angle mounting, J1 and J2 axis motion range are restricted.
 Note 2) During short distance motions, the axis speed may not reach the maximum value stated.
 Note 3) Compliant with ISO9283.
 Note 4) Without controller.



FANUC AMERICA CORPORATION
 3900 WEST HAMLIN ROAD
 ROCHESTER HILLS MI 48309-3253

