

CRX-25iA



Max. load capacity
at wrist: 25/30 kg



Max. reach
(end of flange):
1889 mm

FANUC

Robot			Max load capacity at wrist (kg)	****Reach (mm)	Controlled axes	***Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						**Maximum speed [°/s]		****Allowable Wrist Load			Input power source (VAC)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	Collaborative Mode [mm/sec]	High Speed Mode [mm/sec]	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard	Wrist & J3 arm
CRX	iA	25	25 30	1889 1756*	6	± 0.05	135	360	360	540	380	360	450	1000	2000	100.0/ 4.7	74.0/ 4.00	32.0/ 2.00	100-120 200-240	IP67	IP67

● standard ○ on request - not available *Operating space is restricted when 30kg payload mode is selected **Please set motion speed according to risk assessment of system. ***Based on ISO9283 ****Nm/Kg.m² *****At the end of flange

CRX-25iA Food-Grade Variant

NSF H1 food-grade grease,
White USDA compliant epoxy coating



CRX-25iA

