

M-900iA/150P



Max. load capacity
at wrist: 150 kg



Max. reach:
3507 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
M-900	iA	150P	150	3507	6	± 0.3	1860	360	180	180	720	250	720	110	95	95	120	120	200	1666/313.6	1666/313.6	715.4/225.4	5	IP54	IP67

● standard ○ on request - not available () with hardware and/or software option ** Based on ISO9283

M-900iA/150P Pedestal/rack mount



M-900iA/150P

