

M-900iA/200P



Max. load capacity
at wrist: 200 kg



Max. reach:
3507 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/Inertia (N·m/kg·m ²)	J5 Moment/Inertia (N·m/kg·m ²)	J6 Moment/Inertia (N·m/kg·m ²)	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard optional	Wrist & J3 arm standard/optional
M-900	iA	200P	200	3507	6	± 0.3	2670	360	180	180	720	230	720	110	95	95	95	95	165	2200/ 431.2	2200/ 431.2	715/ 392	10	IP54	IP67

● standard ○ on request - not available [] with hardware and/or software option ** Based on ISO9283

M-900iA/200P Pedestal/rack mount



M-900iA/200P

