

# CR-15iA

# FANUC



Max. load capacity  
at wrist: 15 kg



Max. reach:  
1441 mm

Robot			Series	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°]						Maximum speed [°/s]						J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption [kW]	Protection	
J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6																	
CR	iA	15	15	15	1441	6	± 0.02**	255	340/ 370***	180	312	380	280	900	800*	800*	800*	800*	800*	800*	26/ 0.9	26/ 0.9	11/ 0.3	1	IP54	IP67	Body standard	Wrist & J3 arm

● standard   ○ on request   - not available   \* max. cartesian speed 800mm/sec (1500mm/sec. when safety monitored)   \*\* Based on ISO9283   \*\*\*Option

CR-15iA

Hollow wrist



CR-15iA

