

M-1*i*A/0.5SL



Max. load capacity
at wrist: 0.5 kg



Max. reach:
420 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-1	iA	0.5SL	0.5(1)	420	4	± 0.03	23 *2)	ø 420 X 150 [*3]				720		-	-	-	3000			*4)			0.2	IP20	IP20

● standard ○ on request - not available *2) with stand () with hardware and/or software option *3) ø in mm by height in mm *4) refer to the wrist load diagram

M-1*i*A/0.5SL 4-axis, long arm



M-1*i*A/0.5SL

