

M-2iA/6HL



Max. load capacity at wrist: 6 kg



Max. reach: 1130 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6					Body standard/optional	Wrist & J3 arm standard/optional
M-2	iA	6HL	6	1130	3	±0.1	125	∅ 1130 X 400 (*3)			-	-	-	-	-	-	-	*4)	NA	2.5	IP69K	IP69K			

● standard ○ on request - not available *3) ∅ in mm by height in mm *4) refer to the wrist load diagram

M-2iA/6HL 3-axis, long arm, hollow wrist



M-2iA/6HL

