

ARC Mate 50iD/7L



Max. load capacity
at wrist: 7 kg




Max. reach:
911 mm

FANUC


Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						Maximum speed [°/s]						Moments (N·m)/Inertia (kg·m ²)			Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia		Body standard/optional	Wrist & J3 arm standard/optional
ARC Mate 50	iD	7L	7	911	6	± 0.01**	27	340 (360)	245	430	380	250	720	370	310	410	550	545	1000	16.6 / .47	16.6 / .47	9.4 / .15	0.5	IP67	IP67

[option] ● standard ○ on request - not available () with hardware and/or software option ** Based on ISO9283

ARC Mate 50iD/7L Long arm



ARC Mate 50iD/7L



» If applied load on the robot exceeds 5kg when the robot is installed on an angle, the operating area is limited by the mount angle. If payload is less than 5kg, there is no restriction of the operating space.