

# M-710iD/70

**FANUC**



Max. load capacity  
at wrist: 70 kg



Max. reach:  
2104 mm

Series	Version	Type	Max.load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°) ***						Maximum speed (°/s)						Moments (N·m)/Inertia (kg·m²)			Protection	
								J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption (kW)	
M-710	iD	70	70	2104	6	± 0.03*	580**	370	225	440	720	250	720	180	180	180	260	260	370	300/30	300/30	150/15	2.5	IP54/IP67

● standard    ○ on request    - not available    \* Based on ISO9283    \*\*Without controller    \*\*\*During short distance motions, the axis speed may not reach the maximum value stated

M-710iD/70

6-axis



M-710iD/70

