




Extended-reach, high-performance paint robot

P-250iB/15 Floor Rail




- The P-250iB Floor Rail is available in both In-Booth and Cleanwall configuration.
- P-250iB Full and Restricted Envelopes are available with Cleanwall Rail.
- Single/Dual P-250iB Robot - Available rail lengths from 3.0m to 11.76m.


P-250iB/15 Cleanwall Floor Rail




P-250iB/15 In-Booth Floor Rail




P-250iB/15 Cleanwall Floor Rail - Restricted Envelope




P-250iB/15 Cleanwall Floor Rail - Restricted Envelope




P-250iB/15 Cleanwall Floor Rail - Full Envelope




P-250iB/15 Cleanwall Floor Rail - Full Envelope



P-250iB/15 In-Booth Floor Rail - Full Envelope



P-250iB/15 In-Booth Floor Rail - Full Envelope



P-250iB/15 Cleanwall Floor Rail - Technical Data

BOOTH LENGTH	RAIL MODULE LENGTH (mm)	RAIL OVERALL LENGTH (mm)	ENVELOPE (mm)	SOFTWARE LIMIT (mm)			INSTALLATION CLEARANCE (mm)
				SINGLE ARM R1, R2	DUAL ARM R4, R3	DUAL ARM R2, R1	
4 M	3900	3916.2	2700	± 1350	+425 / -1350	+1350 / -425	41.9
6 M	5880	5896.2	4680	± 2340	+1415 / -2340	+2340 / -1415	51.9
8 M	7800	7816.1	6600	± 3300	+2375 / -3300	+3300 / -2375	91.95
10 M	9780	9796.2	8580	± 4290	+3365 / -4290	+4290 / -3365	101.9
12 M	11760	11776.2	10430	+5280 / -5215	+4290 / -5215	+5215 / -4290	111.9
10 FT	3000	3016.2	1800	± 900	N/A	N/A	15.9
15 FT	4500	4516.2	3300	± 1650	+725 / -1650	+1650 / -725	27.9
20 FT	5880	5896.2	4680	± 2340	+1415 / -2340	+2340 / -1415	99.9
25 FT	7500	7516.2	6300	± 3150	+2225 / -3150	+3150 / -2225	51.9
30 FT	9000	9016.2	7800	± 3900	+2975 / -3900	+3900 / -2975	63.9
35 FT	10380	10396.2	9050	+4590 / -4525	+3665 / -4590	+4590 / -3665	135.9
40 FT	11760	11776.2	10430	+5280 / -5215	+4290 / -5215	+5215 / -4290	207.9

P-250iB/15 In-Booth Floor Rail - Technical Data

BOOTH LENGTH	RAIL MODULE LENGTH (mm)	RAIL OVERALL LENGTH (mm)	ENVELOPE (mm)	SOFTWARE LIMIT (mm)			INSTALLATION CLEARANCE (mm)
				SINGLE ARM R1, R2	DUAL ARM R4, R3	DUAL ARM R2, R1	
4 M	3900	3945	2700	± 1350	+425 / -1350	+1350 / -425	27.5
6 M	5880	5925	4680	± 2340	+1415 / -2340	+2340 / -1415	37.5
8 M	7800	7845	6600	± 3300	+2375 / -3300	+3300 / -2375	77.5
10 M	9780	9825	8580	± 4290	+3365 / -4290	+4290 / -3365	87.5
12 M	11760	11805	10430	+5280 / -5215	+4290 / -5215	+5215 / -4290	97.5
10 FT	3000	3045	1800	± 900	N/A	N/A	1.5
15 FT	4500	4545	3300	± 1650	+725 / -1650	+1650 / -725	13.5
20 FT	5880	5925	4680	± 2340	+1415 / -2340	+2340 / -1415	70.5
25 FT	7500	7545	6300	± 3150	+2225 / -3150	+3150 / -2225	37.5
30 FT	9000	9045	7800	± 3900	+2975 / -3900	+3900 / -2975	49.5
35 FT	10380	10425	9050	+4590 / -4525	+3665 / -4590	+4590 / -3665	121.5
40 FT	11760	11805	10430	+5280 / -5215	+4290 / -5225	+5225 / -4290	193.5